


SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs



LCCN45876

Configuration

- SMB Plug Connector
- 50 Ohms
- Straight Body Geometry
- PCB Interface Type
- Solder Attachment
- PCB
- Non-Magnetic Design

Features

- Max. Operating Frequency 4 GHz
- Excellent VSWR of 1.06:1
- Gold over Copper Plated Bronze Contact
- Magnetic Susceptibility 10^{-5}

Applications

- General Purpose Test
- Custom Cable Assemblies
- Medical
- Military and Aerospace
- Quantum Computing

Description

SMB Non-Magnetic Straight Plug Receptacle for PCB Solder Legs type Connector LCCN45876 from L-Com is in stock at our warehouse and ready to ship on the same-day of your order. The LCCN45876 is a SMB Non-magnetic straight Plug receptacle for PCB solder legs type Connector. These Non-Magnetic Connector frequency ranges from 0-4 GHz with 50 Ohms impedance.

Our RF coaxial connector specialists are available to answer any questions or concerns you have on the LCCN45876 SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs. Our Non-magnetic connectors have a susceptibility of around 10^{-5} , as opposed to 10^{-2} for standard connectors made of brass/nickel materials. As a result, our non-magnetic connectors are transparent to the magnetic field, which means no field distortion and a higher Signal-to-Noise Ratio (SNR).

Contact L-Com's expert technical support for assistance with the SMB Non-Magnetic straight Plug receptacle for PCB solder legs type Connector or any RF coaxial cable connectors or cable assemblies. Download our LCCN45876 datasheet with specifications and CAD drawing with dimensions for details. Our knowledgeable sales team simplifies the purchasing process and ensures that your SMB Non-magnetic RF coaxial connector will be exact to your specifications. The target audience for the straight coaxial plug is for quantum computing, the military and aerospace industries as well as the medical industry including MRI and patient monitoring devices.


The LCCN45876 connector from L-Com uses a dedicated manufacturing process and raw material selection to guarantee the low magnetic susceptibility level of the connectors. The SMB straight RF coax connector is available now from L-Com. We have no MOQ (minimum order quantity) and the connector ships the very same day from our warehouse.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.06:1	
Insertion Loss			0.03	dB
Operating Voltage (AC)			500	Vrms
Dielectric Withstanding Voltage (AC)			1,000	Vrms
Insulation Resistance	1,000			MOhms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs LCCN45876](#)

SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs



LCCN45876

RF Leakage	57	dB
------------	----	----

Mechanical Specifications

Size	
Length	28.26 in [717.80 mm]
Width	24.45 in [621.03 mm]
Height	24.45 in [621.03 mm]
Weight	0.04 lbs [18.20 g]
Mating Cycles	500 Cycles

Material Specifications

Description	Material	Plating
Contact	Bronze	Gold over Copper
Body	Bronze	Copper-Tin-Zinc Alloy

Environmental Specifications

Temperature	
Operating Range	-65deg C to +165deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs LCCN45876

URL: <https://www.l-com.com/smb-straight-jack-receptacle-non-magnetic-pcb-solder-legs-lccn45876-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

SMB Straight Plug Receptacle Non-Magnetic for PCB Solder Legs

L-com CAD Drawing

