

## 14"x12"x7" 120 VAC Black Industrial Enclosure with Mounting Plate and Heater Model: NBB141207-1H0

### Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment installations
- Corrosive environments
- Security and surveillance equipment installations

### Features

- Molded black fiberglass reinforced polyester (FRP) enclosure with integral mounting flanges
- Fully gasketed lid with stainless steel quick release latches with padlock hasps
- NEMA Type 4, 4X / IP66 rated
- Features aluminum mounting plate with surge protected duplex 120 VAC outlets & thermostat controlled heating system



### Description

The NBB141207-1H0 is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester (FRP), it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface without the need for extra mounting hardware. The fully gasketed raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The black color of the NBB series makes these enclosures ideal for security and surveillance equipment since they blend in easier with existing municipality landscapes. The contoured body provides an attractive and contemporary appearance.

### 120 VAC Mounting Plate with Lightning Protection

The aluminum mounting plate features standard surge protected duplex 120 VAC outlets and a terminal block for easy hook up to the externally provided line power. In addition, the unit can accept up to two optional bulkhead-mount N-Type lightning protectors to protect the coaxial cable runs.

### Cold Environments

To help ensure trouble-free operation of electronic equipment, proper operating temperatures inside an enclosure needs to be maintained. With the built-in heating system, internal temperatures can be better maintained. This model is ideal in Cold environments.

The NBB141207-1H0 includes a thermostat-controlled 200W heating system. The heater turns on when the internal temperature drops to 40° F (4° C) ±7° and turns off at 60° F (15° C) ±5°. The heater does not require the use of any of the AC outlets, leaving them all available for your equipment. No extra room for the heater is required since it is mounted underneath the plate.

### Optional Pole Mounting Kits

Available on the L-com web site, these optional kits allows the enclosure to be mounted on poles ranging from 1.2 to 11 inches in diameter.

### Specifications

<b>Enclosure Material</b>	Halogen free, self-extinguishing fiberglass reinforced polyester (FRP)
<b>Enclosure Color</b>	Black
<b>Voltage</b>	120 VAC
<b>Heater Power</b>	200 Watts
<b>Weight</b>	10.8 lbs (4.9 kg)
<b>Mounting Plate Material</b>	.10" (2.5mm) Thick Anodized Aluminum
<b>Mounting Plate Dimensions</b>	12.7 x 10.8 in. (322 x 274 mm)
<b>Outside Dimensions (max)</b>	15.5 x 13.3 x 8.3 in. (393 x 338 x 201 mm)
<b>Inside Dimensions</b>	14.0 x 12.0 x 5.8 in. (356 x 305 x 147 mm)
<b>Flame Rating</b>	UL 94-5V
<b>RoHS Compliant</b>	Yes
<b>Cable Feed</b>	1/2" Cable Conduit Connector
<b>Ratings*</b>	NEMA Type 4, 4X / IP66

\*Note: Enclosure ports (Cable conduit connector and N-type holes for lightning protectors or connectors) must be properly sealed to maintain NEMA TYPE 4, 4X / IP66 rating.

Temperature Controller Specifications	
<b>Heater Turn-On Temperature</b>	+40° F (4° C) ±7°
<b>Heater Turn-Off Temperature</b>	+60° F (15° C) ±5°

