

2 Port Optical Fiber Information Panel with SC/UPC Pigtailed and SC/UPC Adapter



LCFTB-E-SC

Features

- 2 Simplex SC/UPC Couplers & 2 SC/UPC Pigtailed included
- Cable Management Tray designed to securely and safely hold your fiber strands
- Low Profile Wall Mounted Fiber Information Panel design
- Integrated mounting holes for securing to any flat surface

Applications

- FTTH Access Networks
- Telecommunication Networks
- CATV Networks
- Data Communications Networks
- Local Area Networks

Description

Indoor Wall Mounted, Single Door Optical Fiber Information Panel is ideal for end terminations of fiber optic runs in residential or commercial buildings. The LCFTB-E-SC comes with 2 Simplex SC/UPC Coupler Ports installed with 2 Simplex SC/UPC Single mode Pigtailed ready for splicing.

Mechanical Specifications

Size

Outer Height	3.9 in	[99.06 mm]
Outer Width	3.2 in	[81.28 mm]
Outer Depth	0.9 in	[22.86 mm]
Weight	0.2 lbs	[90.72 g]
Enclosure Material	ABS Plastic	

Environmental Specifications

Operating Temperature -40 to 60 deg C

2 Port Optical Fiber Information Panel with SC/UPC Pigtailed and SC/UPC Adapter from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2 Port Optical Fiber Information Panel with SC/UPC Pigtailed and SC/UPC Adapter LCFTB-E-SC




URL: <https://www.l-com.com/2-port-optical-fiber-information-panel-with-sc-upc-pigtailed-and-sc-upc-adapter-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

2 Port Optical Fiber Information Panel with SC/UPC Pigtails and SC/UPC Adapter


L-com CAD Drawing

REVISIONS		
REV.	DESCRIPTION	DATE
A	INITIAL RELEASE	01/15/2021
		APPROVED TOZA

DIMENSIONS ARE FOR REFERENCE ONLY.
DIMENSIONS ARE SHOWN IN MILLIMETERS.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED READING DIMENSIONS ARE IN INCHES DIMENSIONS IN [] ARE IN MILLIMETERS TOLERANCES: .X = ±.2 (5.08) FRACTIONS .XX = ±.02 (.51) ± 1/32 .XXX = ±.005 (.13) ANGLES ± 1° CABLE LENGTH (L) TOLERANCES: L ≤ 12 (305) ± 1 (25) / -0 12 (305) < L ≤ 60 (1524) = +4 (102) / -0 60 (1524) < L ≤ 120 (3048) = +4 (102) / -0 120 (3048) < L ≤ 300 (7620) = +6 (152) / -0 300 (7620) < L = +5% / -0 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	 <p>an INFINITE brand 50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 Fax: 1.978.689.9484 Website: www.L-com.com E-mail: CustomerService@L-com.com</p>	THE INFORMATION AND DRAWINGS HEREON IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED. SHEET 1 OF 1 SCALE N/A THE INFORMATION AND DRAWINGS HEREON IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.
--	--	---

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DZINN	LCFTB-E-SC	A