

## Weatherproof 14" x 10" x 4" Wireless Enclosure with 120 VAC Power Module

Model: NBP141004-100


### Applications and Features

#### Features:

- Compact Weatherproof Molded ABS Enclosure
- Fully gasketed padlockable raised lid
- NEMA Type 3, 3X / IP55 rated
- Removable 120 VAC power module
- Heavy duty Hook-and-Loop tape for mounting equipment in enclosure
- Also available in 4-Packs (Item# NBP141004-100-4)

#### Applications:

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage



## Product Description

### Secure your wireless equipment...

Remote wireless equipment such as access points, routers and bridges [see below] often are more vulnerable to tampering and theft. This can disrupt and even cripple critical communications. A low cost solution for protecting and securing your wireless equipment is the NBP141004-100. This rugged, weatherproof composite enclosure is ideal for both indoor and outdoor applications. The compact size of this enclosure makes it ideal for locations with limited space requirements such as equipment closets or mobile applications. Also due to its size, the NBP141004-100 can be used where aesthetics are important, such as in offices and in public areas requiring Hotspots.


The 10.5" x 9.5" x 4" (266 x 241 x 101 mm) compartment features a removable power module with two 120 VAC outlets. This power module has provisions to install two additional outlets. Cable access to the inside of the enclosure is via three rubber cable glands located on the bottom. Equipment can be mounted inside the enclosure by using the included hook-and-loop tape. The raised lid features a continuous gasket and a quick release latch with provisions for a padlock. The enclosure material is molded UV stabilized ABS. Three gasketed mounting holes are provided inside the enclosure for easy installations.

## Specifications

Model	NBP141004-100
Power Module Voltage	120 VAC
Enclosure Material	Molded UV Stabilized ABS
Enclosure Color	Gray
Weight	4 lbs (1.8 kg)
Outside Dimensions (max)	14.5 x 10.8 x 4.3 inches (36.8 x 27.4 x 10.9 cm)
Inside Dimensions	10.5 x 9.5 x 4 inches (26.6 x 24.1 x 10.1 cm)
Cable Feed	(3) 9/16" (14.2mm) Rubber Cable Glands
Ratings	NEMA 3, 3X / IP55

Model: NBP141004-100

**Enclosure Dimensions**



**Configuration Examples**

<p><b>Shown with U.S.Robotics® USR5450 Access Point</b></p>  <p>Shown with U.S. ROBOTICS USR5450 Access Point (not included)</p>	<p><b>Shown with Linksys® WAP54G Access Point</b></p>  <p>Shown with Linksys WAP54G Access Point (not included)</p>	<p><b>Shown with D-Link® AirPlus Extreme Wireless Router</b></p>  <p>Shown with D-Link AirPlus Extreme Wireless Router (not included)</p>
---	--	--