


75 Ohm Low Loss Flexible LMR-400-75 Indoor / Outdoor Rated  
Coax Cable Double Shielded with Black PE Jacket



**LMR-400-75**



**Configuration**

- Low Loss, Outdoor Flexible Cable
- 2 Shield(s)

**Features**

- PE Jacket
- Max operating temperature 85°C
- Min Install Bend radius of 4 inches
- Phase Velocity 85% VoP
- Max operating Frequency of 2.5 GHz

**Applications**

- Antenna Installs
- RF Test systems
- General Purpose RF Interconnect
- Laboratory applications

**Description**

LMR-400-75 coax cable from L-com is only one of a large number of radio frequency coaxial cable types specifically stocked to be ready for quick shipment. L-com Microwave LMR-400-75 coax cable is manufactured in a flexible design and has a 75 Ohm impedance. This low loss flexible 75 Ohm coax cable LMR-400-75 is constructed with a 0.405 inch diameter and Black PE jacket.

LMR-400-75 flexible 50 Ohm coax cable with PE jacket is rated for a 2.5 GHz maximum operating frequency. This 75 Ohm 0.405 inch diameter and low loss flexible coax cable is built with a double shield count and RF shielding of 90 dB. L-com Microwave LMR-400-75 coax is constructed with PE (F) dielectric and a maximum operating temperature of 85 degrees C. Times Microwave LMR-400-75 coax cable specs for this wire properties can be found on its RF coax cable LMR-400-75 datasheet.


LMR-400-75 cable is part of more than one million RF, microwave parts in stock at L-com. This Times Microwave low loss LMR-400-75 coax cable is ready to buy and can be shipped worldwide. L-com also maintains a wide selection of other radio frequency coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave components.

\* LMR™ is a trademark of Times Microwave Systems.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2.5	GHz
Impedance		75		Ohms
Velocity of Propagation		85		%
Shielding Effectiveness	90			dB
Dielectric Withstanding Voltage (DC)			2,000	Vdc
Jacket Spark			5,000	Vrms
Nominal Capacitance		15.9 [52.17]		pF/ft [pF/m]
Nominal Inductance		0.09 [0.3]		uH/ft [uH/m]
Input Power (Peak)			10	kWatts

75 Ohm Low Loss Flexible LMR-400-75 Indoor / Outdoor Rated  
Coax Cable Double Shielded with Black PE Jacket



**LMR-400-75**



**Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units
Frequency	50	150	220	450	900	MHz
Attenuation, Typ	0.8	1.5	1.8	2.6	3.7	dB/100ft
	2.62	4.92	5.91	8.53	12.14	dB/100m
Input Power (CW), Max	2,310	1,320	1,080	740	520	Watts

Description	F6	F7	F8	F9	F10	Units
Frequency	1.5	1.8	2	2.5		GHz
Attenuation, Typ	4.9	5.4	5.7	6.4	4	dB/100ft
	16.08	17.72	18.7	21	13.12	dB/100m
Input Power (CW), Max	390	350	330	300		Watts

**Mechanical Specifications**

Diameter	0.405 in [10.29 mm]
Weight	0.07 lbs/ft [0.1 Kg/m]
Min. Bend Radius (Installation)	1 in [25.4 mm]
Min. Bend Radius (Repeated)	4 in [101.6 mm]
Bending Moment	0.5 lbs-ft [0.68 N-m]
Tensile Strength	160 lbs [72.57 kg]
Flat Plate Crush	40 lbs/in [0.71 Kg/mm]

**Construction Specifications**

Description	Material and Plating	Diameter
Inner Conductor	Beryllium Copper 1 Strand(s)	0.065in [1.65mm]
Conductor Type	Solid	
Dielectric	PE (F)	0.285in [7.24mm]
First Shield	Aluminum Tape	
Second Shield	Tinned Copper	
Jacket	PE, Black	0.405in [10.29mm]

75 Ohm Low Loss Flexible LMR-400-75 Indoor / Outdoor Rated  
Coax Cable Double Shielded with Black PE Jacket



## LMR-400-75



### Environmental Specifications

#### Temperature

Operating Range

-40°C to 85°C

Storage Range

-70°C to 85°C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

75 Ohm Low Loss Flexible LMR-400-75 Indoor / Outdoor Rated Coax Cable Double Shielded with Black PE Jacket from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

75 Ohm Low Loss Flexible LMR-400-75 Indoor / Outdoor Rated  
Coax Cable Double Shielded with Black PE Jacket

L-com CAD Drawing

