

14x12x07 UL Listed Stainless Steel Weatherproof
Outdoor IP66 NEMA 4X Enclosure



NBSS141207

Features

- UL[®] Listed 16ga. Brushed 304 Stainless Steel
- 304 Stainless steel latch with padlock eye
- NEMA Type 4X / IP66* rated
- Fully gasketed lid, integral welded mounting flange & 316 Stainless steel hinge and removable pin

Applications

- Electrical & Electronics Instruments, Controls & Components, Wireless LAN WiFi equipment
- Indoor and outdoor installations
- Rapid Deployment Installations
- EMI/RFI Sensitive environments/equipment
- Protection of equipment from theft or damage

Description

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from 16ga. Brushed 304 Stainless Steel that provides superior protection against corrosion, chemicals and wet conditions. The enclosure is constructed with UV protected and impact resistant material to ensure protection in any environment. The integrated welded mounting flange allows the enclosure to be mounted directly to any flat wall surface provided proper screws are used into secure studs. The enclosure can also be mounted to a wide range of pole diameters with one of our optional pole mounting hardware kits. The fully gasketed lid features a 316 stainless steel removable hinge pin that allows for quick removal & reattachment with only a pair of pliers. The enclosure comes with a 304 stainless steel latch with padlock eye allowing you to secure the enclosure from tampering.

The NBSS141207 is ideal for custom applications, which may require special modifications to the enclosure. Mounting stand-offs inside the enclosure can be used for mounting one of our blank accessory plates like the aluminum HGX-NPLATE01 or the non-metallic star-board HGX-NPLATE08.

The HGX-PMT series of pole mounting kits allow the populated enclosure to be securely mounted to a variety of different size poles.

The NBSS141207 comes with a UL Listing Mark in every enclosure. Ideal for all construction sites and equipment enclosure applications.

Compatible versions include HGX-PMT13, HGX-PMT16, HGX-PMT28, HGX-PMT29, HGX-PMT30 & HGX-PMT33

*Note: Any holes or openings you might introduce must be properly sealed to maintain NEMA Type 4X / IP66 rating

Size

Outer Height	14.5 in	[368.3 mm]
Outer Width	13 in	[330.2 mm]
Outer Depth	7.83 in	[198.88 mm]
Inner Height	14.4 in	[365.76 mm]
Inner Width	12 in	[304.8 mm]
Inner Depth	7.69 in	[195.33 mm]
Weight	17.2 lbs	[7.8 kg]
Enclosure Material	304 Stainless Steel	

Environmental Specifications

Temperature Rating	-40° to 320°F [-40° to 160°C]
NEMA Rating	4X
Ingress Protection (IP) Rating	IP66

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[14x12x07 UL Listed Stainless Steel Weatherproof Outdoor IP66 NEMA 4X Enclosure NBSS141207](#)

14x12x07 UL Listed Stainless Steel Weatherproof
Outdoor IP66 NEMA 4X Enclosure

NBSS141207



Compliance Certifications

UL Listed

E337864

14x12x07 UL Listed Stainless Steel Weatherproof Outdoor IP66 NEMA 4X Enclosure from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 14x12x07 UL Listed Stainless Steel Weatherproof Outdoor IP66 NEMA 4X Enclosure NBSS141207


URL: <https://www.l-com.com/nema-enclosures-14x12x07-ul-listed-stainless-steel-weatherproof-nema-4x-enclosure-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

14x12x07 UL Listed Stainless Steel Weatherproof Outdoor IP66 NEMA 4X Enclosure

L-com CAD Drawing



APPROVALS	DATE	50 HIGH STREET NORTH ANDOVER, MA 01845
DRAWN BY: DUNN	07/05/2019	L-com Global Connectivity
DESIGNED BY: DUNN	07/05/2019	
APPROVED BY: MMARINER	07/10/2019	ENCLOSURE
UNLESS OTHERWISE SPECIFIED:	PRODUCT DESCRIPTION	Enclosure Stainless Steel 14x12x07"
DIMENSIONS MAY VARY	REV. NO.	B 43321
COLOR OPTIONS MAY VARY	SCALE	NBS S1 41 207
		SHEET 1 OF 1