

# 18x16x8 Inch Vented Weatherproof Enclosure with 802.3af Compatible (PoE) Power-Over-Ethernet Interface - Model: NB181608-40V

# **Applications and Features**

#### Features:

- Molded Fiberglass Reinforced Polyester (FRP) industrial Enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Fully gasketed raised Vented lid with removable filters & integral mounting flange
- Features aluminum mounting plate with 802.3af compatible PoE Interface with CAT 5 Surge Protection

# **Applications:**



- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Extreme temperature environments
- Rapid Deployment Installations
- · Protection of equipment from theft or damage





## **Product Description**

#### Start with the Box...

The box is a rugged  $18" \times 16" \times 8"$  weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass, it is well suited for high temperature or corrosive environments. The mounting flange allows it to be wall mounted as well as on a flat surface. The box can also be pole mounted with the optional pole mounting hardware kit. The fully gasketed lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The enclosure material is UV stabilized and comes in machine tool gray. The enclosure also features holes for mounting Lightning Protectors or Connectors, a grounding lug and  $\frac{1}{2}$  cable conduit connector.

#### **Mounting Plate**

The aluminum mounting plate has provisions to mount WLAN equipment from Cisco®, Symbol®, D-Link®, HyperLink and more (see mounting plate drawing). With the optional HGX-AMOUNT02 bracket a wide array of HyperLink Amplifiers, Power-Over-Ethernet products and Power Supplies can be mounted as well. Two of these brackets can be mounted side by side. Also available is the HGX-NMOUNT03 Universal Mounting Shelf that can be attached to the mounting plate and can accommodate additional equipment to be placed in the enclosure.

#### **Power-Over-Ethernet (PoE)**

The Mounting Plate features an 802.3af compatible PoE interface with CAT 5 surge protection. The interface includes Lightning Protection and support for normal and reverse polarity POE equipment. An optional 802.3af compatible PoE interface with surge protector can be added for a second CAT5 cable.

#### **Vented Enclosure**

The NB181608-40V features a vented lid with removable filters and vent covers on the outside of the enclosure.

## **Lightning Protection**

The PoE interface features built in lightning protection. This helps add an extra level of protection to PoE equipment installed in the enclosure. In addition, the unit can accept up to two optional bulkhead-mount N-Type lightning protectors to protect the coaxial cable runs.

### **Specifications**

Enclosure Material	Fiberglass Reinforced Polyester
Enclosure Color	Machine Tool Gray
Mounting Plate Material	.10 in. (2.5mm) Thick Anodized Aluminum
Mounting Plate Dimensions	16.8 x 14.8 inches (42.6 x 37.5 cm)
Weight	19 lbs (8.6 kg)
Outside Dimensions (max)	19.5 x 17.5 x 10 inches (49.5 x 44.4 x 25.4 cm)
Inside Dimensions	17.7 x 15.7 x 8.5 inches (44.9 x 39.9 x 21.6 cm)
Flame Rating	UL 94-5V
Cable Feed	1/2" Cable Conduit Connector
RoHS Compliant	Yes
Ratings	NEMA Type 3R, 3RX / IP24



## **Enclosure Dimensions**

