

Passive CWDM, Rugged Cassette Mux, 16 Ch Custom (skip 1391-1411nm) w/ 20nm spacing, start w/ ch 1270nm, 1m 900um fiber.



## PCWLM-CA327-19NN

### Features

- Passive
- CWDM
- 20nm spacing
- Rugged Field Cassette (120x85x20mm)
- Single Fiber Mux
- 16 Channels (skipping 1391 & 1411nm)
- Starting with channel 1271nm
- 1m 900um fiber leads
- industrial temperature (-40c ~ 85c)

### Applications

- Single Mode Fiber Networking
- Single Fiber
- Mux function
- Metro transport
- Regional Distribution
- Outside Plant (OSP) Operation

### Description

The L-COM PCWLM-CA327-19NN is a CWDM Passive Filter with 16 CWDM Channels. The L-COM PCWLM-CA327-19NN is a 120x85x20mm field cassette filter with mux functionality. The L-COM PCWLM-CA327-19NN is rated for industrial temperature function (-40c to +85c) for applications such as outside plant installation. The L-COM PCWLM-CA327-19NN has 16 channels: 1271, 1291, 1311, 1331, 1351, 1371, 1431, 1451, 1471, 1491, 1511, 1531, 1551, 1571, 1591, and 1691nm (skipping 1391 and 1411nm), starting with 1271nm and with 20nm spacing. The L-COM PCWLM-CA327-19NN has 1 meter 900um buffer fiber leads. The L-COM PCWLM-CA327-19NN is a single fiber filter for muxing channels into a COM signal. L-COM produces the high quality passive filters that your business can rely on. With products continually in stock and same-day shipping, our expert technical support and knowledgeable sales team can get you to the right parts for the job.

### Configuration

Connector Type	900um Bare Fiber (1M)
Number of Channels	16
Module Function	Mux
Filter Type	CWDM

### Filter Specifications

Description	Minimum	Typical	Maximum	Units
Operating Wavelength	1260		1635	nm
Pass Band	6.5			nm
Pass Band Ripple			0.5	dB
Center Wavelength (Channel)	1,271		1611	nm
Channel Spacing		20		nm
Channel Insertion Loss			4	dB
Return Loss	45			dB
Directivity			50	dB
PDL			0.25	dB
PMD			0.2	PS
Power Handling			300	mW

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Passive CWDM, Rugged Cassette Mux, 16 Ch Custom \(skip 1391-1411nm\) w/ 20nm spacing, start w/ ch 1270nm, 1m 900um fiber. PCWLM-](#)

Passive CWDM, Rugged Cassette Mux, 16 Ch Custom (skip 1391-1411nm) w/ 20nm spacing, start w/ ch 1270nm, 1m 900um fiber.



## PCWLM-CA327-19NN

IL Thermal Stability	0.005	dB/degC
Wavelength Thermal Stability	0.002	nm/degC

### Environmental Specifications

#### Temperature

Operating Range	-40 to +85 deg C
Storage Range	-40 to +85 deg C
Humidity	5-95 %RH

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Passive CWDM, Rugged Cassette Mux, 16 Ch Custom (skip 1391-1411nm) w/ 20nm spacing, start w/ ch 1270nm, 1m 900um fiber. from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Passive CWDM, Rugged Cassette Mux, 16 Ch Custom (skip 1391-1411nm)  
w/ 20nm spacing, start w/ ch 1270nm, 1m 900um fiber.

**L-com CAD Drawing**

