

# 14"x12"x7" 120 VAC Black Industrial Enclosure with Mounting Plate, Cooling Fan and Heater - Model: NBB141207-1HF

# **Applications**

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment installations
- Corrosive environments
- Security and surveillance equipment installations

#### **Features**

- Molded black fiberglass reinforced polyester (FRP) enclosure with integral mounting flanges
- Fully gasketed lid with stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Features aluminum mounting plate with surge protected duplex 120 VAC outlets & thermostat controlled heating and cooling system







# **Description**

The NBB141207-1HF is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester (FRP), it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface without the need for extra mounting hardware. The fully gasketed lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The black color of the NBB series makes these enclosures ideal for security and surveillance equipment since they blend in easier with existing municipality landscapes. The contoured body provides an attractive and contemporary appearance.

#### 120 VAC Mounting Plate with Lightning Protection

The aluminum mounting plate features standard surge protected duplex 120 VAC outlets and a terminal block for easy hook up to the externally provided line power. In addition, the unit can accept up to two optional bulkheadmount N-Type lightning protectors to protect the coaxial cable runs.

### **Hot and Cold Environments**

To help ensure trouble-free operation of electronic equipment, proper operating temperatures inside an enclosure needs to be maintained. With the built-in Heater and Cooling system, internal temperatures can be better maintained. This model is ideal in Hot and Cold environments.



The NBB141207-1HF includes a thermostat-controlled 200W heating system. The heater turns on when the internal temperature drops to  $40^{\circ}$  F ( $4^{\circ}$  C)  $\pm 7^{\circ}$  and turns off at  $60^{\circ}$  F ( $15^{\circ}$  C)  $\pm 5^{\circ}$ . The heater does not require the use of any of the AC outlets, leaving them all available for your equipment. No extra room for the heater is required since it is mounted underneath the plate.

For cooling, the thermostat-controlled 12W high airflow, low noise fan allows air to be pushed or pulled through the enclosure. Filters for both ports are easily removable for cleaning and replacement. The fan turns on when the internal temperature rises to 120° F (49° C)  $\pm 5^{\circ}$  and turns off at 90° F (32° C)  $\pm 10^{\circ}$ . Like the heater, the cooling fan does not require the use of any of the AC outlets, leaving them all available for your equipment.

# **Optional Pole Mounting Kits**

Available on the L-com web site, these optional kits allows the enclosure to be mounted on poles ranging from 1.2 to 11 inches in diameter.

## **Specifications**

Enclosure Material	Halogen free, self-extinguishing fiberglass reinforced polyester (FRP)
Enclosure Color	Black
Voltage	120 VAC
Fan Power	12 Watt
Heater Power	200 Watt
Weight	12.5 lbs (5.6 kg)
Mounting Plate Material	.10" (2.5mm) Thick Anodized Aluminum
Mounting Plate Dimensions	12.7 x 10.8 in. (322 x 274 mm)
Outside Dimensions (max)	15.5 x 13.3 x 8.3 in. (393 x 338 x 201 mm)
Inside Dimensions	14.0 x 12.0 x 5.8 in. (356 x 305 x 147 mm)
Flame Rating	UL 94-5V
RoHS Compliant	Yes
Cable Feed	1/2" Cable Conduit Connector
Ratings	NEMA 3R, 3RX / IP24

Temperature Controller Specifications	
Cooling Fans Turn-on Temperature	+120° F (49° C) ±5°
Cooling Fans Turn-off Temperature	+90° F (32° C) ±10°
Heaters Turn-On Temperature	+40° F (4° C) ±7°
<b>Heaters Turn-Off Temperature</b>	+60° F (15° C) ±5°



