

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 40CH, 100 GHz spacing, starting ch20 (1561.42nm), LC/UPC connectors, with Mon (%1)



PDW3C-40120-NN44

Features

- Passive
- DWDM
- 100GHz spacing
- 19" Rack Mount
- Two Fiber Mux& Demux Combo
- 40 Channels (20-59)
- Starting with channel 20 (1561.42nm)
- LC/UPC connectors
- 1% Monitor option

Applications

- Single Mode Fiber Networking
- Dual Fiber
- Side by side Mux and DeMux functions
- 40 channels
- Metro transport
- Regional Distribution
- Inside Plant (ISP) Operation

Description

The L-COM PDW3C-40120-NN44 is a DWDM Passive Filter with 40 DWDM Channels. The L-COM PDW3C-40120-NN44 is a 1RU 19" Rack Mount filter with Combo Mux/DeMux functionality. The L-COM PDW3C-40120-NN44 has 40 DWDM channels: ITU CH20-59 starting with Channel 20 (1561.42nm) and with 100GHz channel spacing. The L-COM PDW3C-40120-NN44 has LC/UPC connectors and has Monitor port option on Mux and Demux. The L-COM PDW3C-40120-NN44 is a dual fiber filter with one sending muxed signal and the other receiving a composit signal for demuxing. L-COM produces the high quality passive filters that your business can rely on. With products continually in stock and same-day shipping, our expert technical support and knowledgeable sales team can get you to the right parts for the job.

Configuration

Connector Type	LC/UPC
Number of Channels	40
Module Function	Mux/DeMux
Filter Type	DWDM

Filter Specifications

Description	Minimum	Typical	Maximum	Units
Operating Wavelength	1527.22		1564.68	nm
Pass Band	0.68		0.93	nm
Pass Band Ripple			0.5	dB
Channel Spacing		0.83		nm
Channel Insertion Loss			4	dB
Return Loss	45			dB
Directivity			50	dB
PDL			0.25	dB
PMD			0.2	PS
Power Handling			300	mW
Adjacent Channel Isolation	28			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 40CH, 100 GHz spacing, starting ch20 \(1561.42nm\), LC/UPC connectors, with Mon \(%1\)](#)

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 40CH, 100 GHz spacing, starting ch20 (1561.42nm), LC/UPC connectors, with Mon (%1)



PDW3C-40120-NN44

Non-Adjacent Channel Isolation	40		dB
Channel to Monitor Port IL		26	dB
COM to Monitor Port IL		23	dB
IL Thermal Stability		0.005	dB/degC
Wavelength Thermal Stability		0.002	nm/degC

Environmental Specifications

Temperature

Operating Range

-5 to +65 deg C

Storage Range

-40 to +85 deg C

Humidity

5-95 %RH

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 40CH, 100 GHz spacing, starting ch20 (1561.42nm), LC/UPC connectors, with Mon (%1) from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 40CH, 100 GHz spacing, starting ch20 (1561.42nm), LC/UPC connectors, with Mon (%1)

L-com CAD Drawing

