

# 18"x16"x8" 120 VAC Black Industrial Enclosure with Mounting Plate, Cooling Fan and Heater - Model: NBB181608-1HF

## **Applications**

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment installations
- Corrosive environments
- Security and surveillance equipment installations

#### **Features**

- Molded black fiberglass reinforced polyester (FRP) enclosure with integral mounting flanges
- Fully gasketed lid with stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Features aluminum mounting plate with surge protected duplex 120 VAC outlets & thermostat controlled heating and cooling system







#### **Description**

The NBB181608-1HF is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester (FRP), it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface without the need for extra mounting hardware. The fully gasketed lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The black color of the NBB series makes these enclosures ideal for security and surveillance equipment since they blend in easier with existing municipality landscapes. The contoured body provides an attractive and contemporary appearance. Due to the large size of this enclosure, it can accommodate dual sets of most access points.

#### 120 VAC Mounting Plate with Lightning Protection

The aluminum mounting plate features standard surge protected duplex 120 VAC outlets and a terminal block for easy hook up to the externally provided line power. In addition, the unit can accept up to two optional bulkheadmount N-Type lightning protectors to protect the coaxial cable runs.

## **Hot and Cold Environments**

To help ensure trouble-free operation of electronic equipment, proper operating temperatures inside an enclosure needs to be maintained. With the built-in Heater and Cooling system, internal temperatures can be better maintained. This model is ideal in Hot and Cold environments.



The NBB181608-1HF includes two thermostat-controlled 200W (400W total) heaters. Each heater is controlled by its own thermostat. The heaters turns on when the internal temperature drops to 40° F (4° C)  $\pm$ 7° and turns off at 60° F (15° C)  $\pm$ 5°. The heaters do not require the use of any of the AC outlets, leaving them all available for your equipment. No extra room for the heaters is required since it is mounted underneath the plate.

For cooling, two thermostat-controlled 12W (24W total) high airflow, low noise fans allows air to be pushed or pulled through the enclosure. Filters for both ports are easily removable for cleaning and replacement. The fans turn on when the internal temperature rises to 120° F (49° C)  $\pm 5^{\circ}$  and turns off at 90° F (32° C)  $\pm 10^{\circ}$ . Like the heaters, the cooling fans do not require the use of any of the AC outlets, leaving them all available for your equipment.

### **Optional Pole Mounting Kits**

Available on the L-com web site, these optional kits allows the enclosure to be mounted on poles ranging from 1.2 to 11 inches in diameter.

#### **Specifications**

Enclosure Material	Halogen free, self-extinguishing fiberglass reinforced polyester (FRP)
Enclosure Color	Black
Voltage	120 VAC
Fan Power	12 Watt (24 Watts total)
Heater Power	200 Watt (400 Watts total)
Weight	21.8 lbs (9.9 kg)
Mounting Plate Material	.10" (2.5mm) Thick Anodized Aluminum
Mounting Plate Dimensions	16.8 x 14.8 inches (426 x 375 mm)
Outside Dimensions (max)	19.5 x 17.5 x 9 inches (495 x 444 x 228 mm)
Inside Dimensions	17.7 x 15.7 x 7.6 in. (449 x 399 x 193 mm)
Flame Rating	UL 94-5V
RoHS Compliant	Yes
Cable Feed	1/2" Cable Conduit Connector
Ratings	NEMA 3R, 3RX / IP24

Temperature Controller Specifications	
Cooling Fans Turn-on Temperature	+120° F (49° C) ±5°
Cooling Fans Turn-off Temperature	+90° F (32° C) ±10°
Heaters Turn-On Temperature	+40° F (4° C) ±7°
Heaters Turn-Off Temperature	+60° F (15° C) ±5°



