

18"x16"x8" 120 VAC Vented Black Industrial Enclosure with Mounting Plate, Heater & Solid State Temperature Controller

Model: NBB181608-1HVS

Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment installations
- Corrosive environments
- Security and surveillance equipment installations

Features

- Molded black fiberglass reinforced polyester (FRP) enclosure with integral mounting flanges
- Fully gasketed vented lid with stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Features aluminum mounting plate with surge protected duplex 120 VAC outlets & solid state controlled heating system



Description

The NBB181608-1HVS is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester (FRP), it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface without the need for extra mounting hardware. The fully gasketed lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The black color of the NBB series makes these enclosures ideal for security and surveillance equipment since they blend in easier with existing municipality landscapes. The contoured body provides an attractive and contemporary appearance. Due to the large size of this enclosure, it can accommodate dual sets of most access points.

Vented Enclosure

The NBB181608-1HVS features a vented lid with removable filters and vent covers on the outside of the enclosure.

120 VAC Mounting Plate with Lightning Protection

The aluminum mounting plate features standard surge protected duplex 120 VAC outlets and a terminal block for easy hook up to the externally provided line power. In addition, the unit can accept up to two optional bulkhead-mount N-Type lightning protectors to protect the coaxial cable runs.

Cold Environments

To help ensure trouble-free operation of electronic equipment, proper operating temperatures inside an enclosure needs to be maintained. With the built-in Heating system, internal temperatures can be better maintained. This model is ideal in Cold environments.

The NBB181608-1HVS comes with two 120 VAC 200 watt heating elements. The heaters are controlled by HyperLink's exclusive solid-state temperature controller. The standard unit has a heat turn-on temperature of +16° F (-8.8° C). The controller features improved temperature setpoint accuracy and can be factory modified for other temperature setpoints. The heater is controlled by an integral high current solid-state AC relay. The relay features Zero Cross Detection for EMI reduction. No extra room for the controller is required since it is mounted underneath the plate.

Optional Pole Mounting Kits

Available on the L-com web site, these optional kits allows the enclosure to be mounted on poles ranging from 1.2 to 11 inches in diameter.

Specifications

Enclosure Material	Halogen free, self-extinguishing fiberglass reinforced polyester (FRP)
Enclosure Color	Black
Voltage	120 VAC
Heater Power	200 Watt (400 Watts total)
Weight	20.3 lbs (9.2 kg)
Mounting Plate Material	.10" (2.5mm) Thick Anodized Aluminum
Mounting Plate Dimensions	16.8 x 14.8 inches (426 x 375 mm)
Outside Dimensions (max)	19.5 x 17.5 x 9 inches (495 x 444 x 228 mm)
Inside Dimensions	17.7 x 15.7 x 7.6 in. (449 x 399 x 193 mm)
Flame Rating	UL 94-5V
RoHS Compliant	Yes
Cable Feed	1/2" Cable Conduit Connector
Ratings	NEMA 3R, 3RX / IP24

Temperature Controller Specifications	
Heater Setpoint Temperature	-9° C (+16° F)
Hysteresis Window	5° C (9° F)
Contact L-com for custom Setpoints	

