

14"x10"x4" Vented INDOOR Enclosure Model: NBP141004-40V

Applications

- Compact molded ABS enclosure
- Fully gasketed pad lockable raised lid, vented for indoor convection cooling
- NEMA Type 3R, 3RX / IP24 rated
- 802.3af compatible PoE interface with Cat 5 surge protection
- Heavy duty hook-and-loop tape for mounting equipment in enclosure

Features

- Remote Wireless LAN WiFi equipment installations using Power-over-Ethernet (PoE)
- Rapid Deployment & indoor installations
- Corrosive environments
- Hotspot applications
- Protection of equipment from theft or damage



Description

Secure your wireless equipment...

Remote wireless equipment such as access points, routers and bridges often are more vulnerable to tampering and theft. This can disrupt and even cripple critical communications. A low cost solution for protecting and securing your wireless equipment is the NBP141004-40V. This rugged, molded composite enclosure is ideal for indoor applications requiring equipment cooling air. The compact size of this enclosure makes it ideal for locations with limited space requirements such as equipment closets or mobile applications. Also due to its size, the NBP141004-40V can be used where aesthetics are important, such as in offices and in public areas requiring HotSpots.

The 10.5" x 9.5" x 4" (266 x 241 x 101 mm) compartment features an 802.3af compatible PoE interface with Cat 5 Surge Protection. Cable access to the inside of the enclosure is via three rubber cable glands located on the bottom. Equipment can be mounted inside the enclosure either by using the included hook-and-loop tape or the four mounting stand-offs. The raised lid features a continuous gasket and a quick release latch with provisions for a padlock. The enclosure material is molded UV stabilized ABS. Three gasketed mounting holes are provided inside the enclosure for easy installations.

Specifications

Power Module Voltage	12-48 VDC Power-over-Ethernet
Enclosure Material	Molded UV Stabilized ABS
Enclosure Color	Gray
Weight	4.2 lbs. (1.9kg)
Outside Dimensions (Max.)	14.5 x 10.8 x 4.3 in (36.8 x 27.4 x 10.9 cm)
Inside Dimensions	10.5 x 9.5 x 4 in (26.6 x 24.1 x 10.1 cm)
Cable Feed	(3) 9/16" (14.2mm) Rubber Cable Glands
Ratings	NEMA Type 3R, 3RX / IP24

