


Bulk Cable Specification

TFDL5026 Category 6a High Flex Cable



ITEM		DESCRIPTION
Conductor	No. of Conductors	4 Pairs
	Material	Tinned Copper
	Construction	26 AWG Stranded (7/34)
Insulation	Material	High Density Polyethylene
	Nominal Diameter	.036"
Cross	Material	Polyethylene
Shielding	Material	Aluminized Polyester Tape
	Coverage	100%
Braiding	Material	Tinned Copper
	Coverage	80%
Jacket	Material	Thermoplastic Elastomer
	Color	Teal
	Nominal Diameter	.275" +/- .010 (7.0 mm)

Jacket Marking:
QUABBIN DATAMAX EXTREME HIGH FLEX INDUSTRIAL ETHERNET/IP PATCH CORD CAT 6a SF/UTP P/N 5026 -C(UL)
US TYPE CMX OUTDOOR - CM 4PR 26 AWG 75C SUN RES - RoHS - (LOT DESIGNATOR) (SEQUENTIAL FOOTAGE)

ELECTRICAL PROPERTIES

Dielectric Strength: 500 Vac

Voltage Rating, Max. 300 V

D.C. Resistance, Max. 14.0 ohm

Listings/Ratings

RoHS Compliant