

18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User Adjustable Therm Heat & Fan Drk Gry

NBPC181610-1HFA2



Features

- High-Impact, UV Resistant Polycarbonate (Dark Gray)
- · Stainless steel latches with padlock eye
- NEMA Type 3R / IP24 rated
- Fully gasketed vented lid with filters & user installed wall mounting brackets
- Features aluminum mounting plate with surge protected duplex 120 VAC outlets & adjustable thermostat controlled heating & cooling system

Applications

- Remote Wireless LAN WiFi equipment installations
- · Indoor and outdoor installations
- · Rapid Deployment Installations

- · Corrosive environments & hotspot applications
- · Protection of equipment from theft or damage

Description

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from High-Impact, UV Resistant Polycarbonate material that provides superior durability to impacts and ease of modification while maintaining minimum weight. It is well suited for high temperature or corrosive environments. The lid includes two vents with installed rain guards and filters. The included wall mount brackets come uninstalled and bagged with their hardware inside of the enclosure. Once the brackets are installed the enclosure can be mounted directly to any flat wall surface provided proper screws are used into secure studs. The brackets, once installed, also allow you to use our HGX-PMT pole mount kits. The lid features a non-metallic hinge system that allows for quick removal & can be reattached just as quickly without the need for any tools. The enclosure comes with a pair of stainless-steel latches with padlock eyes allowing you to secure the enclosure from tampering. The enclosure comes in a Dark Gray (Pantone 422C)

Mounting Plate

The aluminum mounting plate included with the NBPC181610-1HFA2 features standard surge protected duplex 120 VAC outlets and a terminal block for easy hook up to externally provided line power. The enclosure also features holes for two N-Bulkhead lightning protectors or connectors, a grounding lug and cable conduit connector.

Heating & Cooling

To help ensure trouble-free operation of electronic equipment, proper operating temperatures inside an enclosure needs to be controlled. With the built-in heaters & dual cooling fans, internal temperatures can be better maintained. This model is ideal in hot and/or cold environments.

For Heating the NBPC181610-1HFA2 includes two thermostat-controlled 200W (400W total) heaters. The heaters do not require the use of any of the AC outlets, leaving them all available for your equipment. No extra room for the heaters is required since they are mounted underneath the plate.

For Cooling the NBPC181610-1HFA2 includes two thermostat-controlled 16.4W (32.8W total) fans. The high airflow, low noise fans allow warm air to be actively pushed out the top vent while the second fan on the lower vent actively pulls in outside air into the enclosure. Filters for both ports prevent foreign objects or debris from entering the enclosure. The cooling fans do not require the use of any of the AC outlets, leaving them all available for your equipment.

User Adjustable Thermostat

The 1HFA2 series features two separate thermostats, allowing the independent control of heating and cooling. The adjustable thermostat provides a temperature range of $+14^{\circ}$ F to $+122^{\circ}$ F for the heating and $+68^{\circ}$ F to $+176^{\circ}$ F for the cooling systems, with a switching difference of 12° F $\pm 7^{\circ}$ F tolerance.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User Adjustable Therm Heat & Fan Drk Gry NBPC181610-1HFA2



18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User Adjustable Therm Heat & Fan Drk Gry

NBPC181610-1HFA2



The heat thermostat features a Normally Closed (NC) circuit. When the temperature rises to the temperature set on the heat adjustment dial the circuit opens which turns off the heaters. When the temperature falls below the temperature set on the heat adjustment dial the circuit closes which turns on the heaters.

The cooling thermostat features a Normally Open (NO) circuit. When the temperature rises to the temperature set on the cooling adjustment dial the circuit closes which turns on the cooling fans. When the temperature falls below the temperature set on the cooling adjustment dial the circuit opens which turns off the cooling fans.

< WARNING >

Recommended Temperature Setting for the Heater should only be between 14° to 40°F

Recommended Temperature Setting for the Fan should only be between 80° to 120°F

Setting the Heater too high and the Fan too low can result in a conflict wherein the unit might try to continue to heat while simultaneously trying to cool it.

The HGX-PMT series of pole mounting kits allow the populated enclosure to be securely mounted to a variety of different size poles.

Compatible versions include HGX-PMT13, HGX-PMT16, HGX-PMT28, HGX-PMT29, HGX-PMT30, & HGX-PMT33

Size

Outer Height	18.9 in	[480.06 mm]	
Outer Width	16.8 in	[426.72 mm]	
Outer Depth	11.3 in	[287.02 mm]	
Inner Height	18.2 in	[462.28 mm]	
Inner Width	16.2 in	[411.48 mm]	
Inner Depth	9.7 in	[246.38 mm]	
Weight	19 lbs	[8.62 kg]	
Enclosure Material	Polycarbon	Polycarbonate	

Environmental Specifications

Temperature Rating	-40° to 265°F [-40° to 129°C]
NEMA Rating	3R
Ingress Protection (IP) Rating	IP24

Compliance Certifications

UL Listed No

18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User Adjustable Therm Heat & Fan Drk Gry from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User Adjustable Therm Heat & Fan Drk Gry NBPC181610-1HFA2



18x16x10 Polycarb Weatherproof NEMA 3R Encl, 120VAC Mnt Plt User Adjustable Therm Heat & Fan Drk Gry

NBPC181610-1HFA2



Adjustable Therm Heat & Fan Drk Gry NBPC181610-1HFA2

URL: https://www.l-com.com/nema-enclosures-18x16x10-polycarb-weatherproof-nema-3r-encl-120vac-mnt-plt-user-adjustable-therm-heat-fan-drk-gry-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

