




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	11/1/01	T CLARK
B	ECN# 1528: REMOVED SCREWS ON MALE SIDE. ADDED VIEW TO SHOW LABEL	10/1/03	T CLARK
C	ECN# 1628: ADDED COMPONENT SPECIFICATIONS TABLE	12/31/03	T CLARK
D	ECN 4547: REVISED SCREW LENGTH AND NEW FORMAT	2/9/10	D.FRISIELLO



FEMALE 24 CONTACT GPIB CONNECTOR



MALE 24 CONTACT GPIB CONNECTOR



NOTES:

MATERIAL:
 HOUSING: DIE-CAST ALUMINUM ALLOY.
 CONNECTOR INSULATORS: GLASS-FILLED PBT, BLUE, UL94V-0 RATED.
 CONNECTOR CONTACTS: 24X, COPPER ALLOY, RIBBON, .085" PITCH.
 THUMBSCREWS: STEEL.

FINISH:
 HOUSING: NICKEL PLATED.
 CONNECTOR CONTACTS: 30μ INCHES GOLD PLATED OVER NICKEL.
 THUMBSCREWS: BLACK OXIDE.

ELECTRICAL:
 VOLTAGE RATING: 200 VOLTS.
 CURRENT RATING: 1 AMP PER CONTACT AT 25 °C.
 INSULATION RESISTANCE: 1 GIGAOHMS

MISCELLANEOUS:
 OPERATING TEMPERATURE RANGE: -40 °C TO +85 °C.
 WIRED STRAIGHT THROUGH, PIN TO LIKE-NUMBERED PIN AND MEETS ANSI/IEEE STD 488.1-1987.
 TWO DUST CAPS PROVIDED FOR CONNECTORS (NOT SHOWN).
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.02 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY T CLARK	10/31/01		
	CHECKED BY D PARHAM	10/31/01	CATEGORY	IEEE-488
	APPROVED BY C McCORMICK	11/1/01	PRODUCT DESCRIPTION	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE	CAD FILE: CIB24XCR.SLDDRW	SHEET 1 OF 1
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CIB24XCR
				REV. D