

Passive CWDM, Field Unit Barrel OADM, 1 Channel 20nm
1550nm, 2m 250um colored bare fiber, Pass Port



PCW5A-01355-24N3

Features

- Passive
- CWDM
- 20nm spacing
- Barrel filter (34mmx5.5mm)
- Single channel OADM
- CWDM 1551nm
- 2m 250um colored fiber leads
- Pass fiber for unused CWDM channels
- industrial temperature (-40c ~ 85c)

Applications

- Single Mode Fiber Networking
- Single Fiber
- single channel OADM function
- Metro transport
- Regional Distribution
- Outside Plant (OSP) Operation

Description

The L-COM PCW5A-01355-24N3 is a CWDM Passive Filter with 1 Channel OADM. The L-COM PCW5A-01355-24N3 is a 34x5.5mm barrel filter with add a single channel to a composite signal or remove a single channel from a composite signal. The L-COM PCW5A-01355-24N3 is rated for industrial temperature function (-40c to +85c) for applications such as outside plant installation. The L-COM PCW5A-01355-24N3 has single channel 1551nm Add/Drop with other channels being passed. The L-COM PCW5A-01355-24N3 has 2 meter 250um colored fiber leads. The PCW5A-01355-24N3 is a single fiber filter for adding or removing a single wavelength from a COM signal. and are used in pairs for implementations using two fibers. L-COM produces the high quality passive filters that your business can rely on. With products continually in stock and same-day shipping, our expert technical support and knowledgeable sales team can get you to the right parts for the job.

Configuration

Connector Type	250um Bare Fiber (2M)
Number of Channels	1
Module Function	OADM
Filter Type	CWDM

Filter Specifications

Description	Minimum	Typical	Maximum	Units
Operating Wavelength	1260		1620	nm
Pass Band	6.5			nm
Pass Band Insertion Loss			1	dB
Pass Band Ripple			0.5	dB
Channel Spacing		20		nm
Return Loss	45			dB
Directivity			50	dB
PDL			0.15	dB
PMD			0.15	PS
Power Handling			300	mW
Adjacent Channel Isolation	30			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Passive CWDM, Field Unit Barrel OADM, 1 Channel 20nm 1550nm, 2m 250um colored bare fiber, Pass Port PCW5A-01355-24N3](#)

Passive CWDM, Field Unit Barrel OADM, 1 Channel 20nm
1550nm, 2m 250um colored bare fiber, Pass Port



PCW5A-01355-24N3

Non-Adjacent Channel Isolation	45	dB
Reflect Channel Isolation	12	dB
Reflect Band Insertion Loss	0.8	dB

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-40 to +85 deg C
Humidity	5-95 %RH

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

Passive CWDM, Field Unit Barrel OADM, 1 Channel 20nm 1550nm, 2m 250um colored bare fiber, Pass Port from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/24/2020	PHOSPODAR

L-com™
an INFINITE brand
 50 High Street, West Mill, 3rd Floor, Suite #30
 North Andover, MA 01845 USA
 Phone: 1.800.341.5266 | 1.978.682.6936
 Fax: 1.978.689.9484
 Website: www.L-com.com
 E-mail: CustomerService@L-com.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGNATION OF THIS DRAWING IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.

SHEET 1 OF 1
 SCALE N/A

SIZE A
 CAGE CODE 43321
 DRAWN BY DFRISIELLO
 ITEM NO. PCW5A-01355-24N3
 REV. A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-Rev:0