


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/30/13	D.GRIFFIN





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMNMAXXX	WHERE XXX = LENGTH IN FEET	CA-NMNMA010 (10 FEET)
CA-NMNMANXX	WHERE NXX = LENGTH IN INCHES	CA-NMNMAN16 (16 INCHES)
CA-NMNMAMXX	WHERE MXX = LENGTH IN METERS	CA-NMNMAM07 (7 METERS)
CA-NMNMAXMX	WHERE MXM = LENGTH IN DECIMAL METERS	CA-NMNMA3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

RoHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	08/30/13	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY P.PESA	08/30/13	PRODUCT DESCRIPTION CA195R NM - NM
	APPROVED BY P.PESA	08/30/13	
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. CA-NMNMA
SCALE: NONE		CAD FILE: CA-NMNMA.SLDDRW	REV. A
SHEET 1 OF 1			