


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3312: CHANGE KIT DETAIL FROM 1AB13-002 TO 1AB13-005	5/2/08	D. GRIFFIN
F	ECN 6469: UPDATED DRAWING FORMAT, PACKAGING, AND LOGOS	10/17/12	D. DESJARDIN





MODEL P/N	LENGTH FT [M]
CCF59-1	1.0 [.30]
CCF59-3	3.0 [.91]
CCF59-6	6.0 [1.83]
CCF59-9	9.0 [2.74]
CCF59-12	12.0 [3.66]
CCF59-25	25.0 [7.62]
CCF59-50	50.0 [15.24]
CCF59-100	100.0 [30.48]

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.

2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	08/21/01	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY ENG	08/21/01	CATEGORY COAXIAL
	APPROVED BY D.PARHAM	08/27/01	PRODUCT DESCRIPTION CA F M/F M RG59B/U
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A FSCM NO. 43321 DWG. NO. CCF59 REV. F SCALE: NONE CAD FILE: CCF59.SLDDRW SHEET 1 OF 1