


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3282: UPDATE DWG FORMAT	4/14/08	D.GRIFFIN



MODEL #	LENGTH	
	FEET	METERS
CCS188A-1	1.0	0.30
CCS188A-1.5	1.5	0.46
CCS188A-2	2.0	0.61
CCS188A-2.5	2.5	0.76
CCS188A-3	3.0	0.91
CCS188A-4	4.0	1.22
CCS188A-5	5.0	1.52
CCS188A-7.5	7.5	2.29
CCS188A-10	10.0	3.05

NOTES:

1. CABLE ASSEMBLY IS DESIGNED FOR HIGH TEMPERATURE APPLICATIONS (165°C)
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
3. INDIVIDUALLY PACKAGE IN A POLYBAG

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY C.MCCORMICK	05/07/2001				
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2[51] / -0 >60 [1524] ≤120 [3048] = +4 / -0 >120 [3048] ≤300 [7620] = +6 / -0 >300 [7620] = +5% / -0%	CHECKED BY D.PARHAM	05/17/2001	CATEGORY COAXIAL			
	ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVED BY R.CARRICK	05/18/2001	PRODUCT DESCRIPTION SMA PLUG TO SMA PLUG;RG188A		
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CCS188A	REV. E
SCALE: NONE			CAD FILE: CCS188A.SLDDRW		SHEET 1 OF 1	