


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/17/13	D.GRIFFIN





WIRING MAP		
"P1"	COLOR	"P2"
1	BLACK	1
2	GRAY	2
3	RED	3
4	GREEN	4
5	BROWN	5
6	BLUE	6
7	ORANGE	7
8	YELLOW	8
9	PURPLE	9
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH FEET [METERS]
CSMNRA9-1MM-1	1.0 [.31]
CSMNRA9-1MM-2.5	2.5 [.76]
CSMNRA9-1MM-5	5.0 [1.52]
CSMNRA9-1MM-10	10.0 [3.05]
CSMNRA9-1MM-15	15.0 [4.57]
CSMNRA9-1MM-25	25.0 [7.62]

- NOTES:**
1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	8/23/13	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	CHECKED BY R.SCOTT	8/23/13	PRODUCT DESCRIPTION <b>CA DB9M/M STR-RA EXIT 1</b>
	APPROVED BY S.SMITH	8/23/13	
PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. CSMNRA9-1MM
SCALE: NONE		CAD FILE: CSMNRA9-1MM.SLDDRW	REV. <b>A</b>
SHEET 1 OF 1			