


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/7/12	D.GRIFFIN
B	ECN 6614: REVISED DIMENSIONS TO RECOMMENDED PANEL CUTOUT	1/11/13	D.FRISIELLO



NOTES:
MATERIAL:
 COUPLER HOUSING: POLYCARBONATE RESIN HIGH-IMPACT UL94V-0 THERMOPLASTIC.
 COLOR, BLACK
 CONTACTS: PHOSPHOR BRONZE, 50 μINCHES GOLD PLATE OVER 100 μINCHES NICKEL PLATE.

ELECTRICAL:
 CURRENT RATING: 1.5 AMPS
 DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS AC.

MISCELLANEOUS:
 OPERATING TEMPERATURE RANGE: -10°C TO +60°C
 APPLICATION: CATEGORY 6.
 WIRING: STRAIGHT THROUGH.
 PANEL THICKNESS: .065" [1.65mm] MAX.
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.

PACKAGING:
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	11/7/12		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY M. SEDLESKI	11/7/12	CATEGORY TELECOM/MODULAR	
	APPROVED BY D. GALLAGHER	11/7/12	PRODUCT DESCRIPTION CPLR RJ45 F/F CAT6 RT ANGLE	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. TDG1026KC-R6	REV. B
			SCALE: NONE	CAD FILE: TDG1026KC-R6.SLDDRW
				SHEET 1 OF 1